

# ACCESSORIES

21st Century SCIENTIFIC, Inc. (800) 448-3680 (208) 667-8800 FAX (208) 667-6600

e-mail: 21st@wheelchairs.com www.wheelchairs.com

IF \*, SEE NOTE LISTED BY STOCK NUMBER ON LAST PAGES

Part Number	Stock Qty Number	Part Description	Suggested Retail Price
<b>BATTERY CHARGERS</b>			
BC24-8 PF	___ A130	24V 8A PowerFirst automatic battery charger	\$440.00
* BC12-6	___ A135	12.6V 6A automatic battery charger	\$316.25
<b>FAN</b>			
FAN	___ A395	Fan with on-off control (complete system)	\$385.00
<b>HORN</b>			
* HORN	___ A501	24V safety audio alert, complete, for most 24V power wheelchairs	\$322.00
HORN PB SWITCH	___ A501P	Supply HORN with pushbutton switch instead of toggle switch, up charge	\$18.98
HORN XLR PWR CBL	___ A502	Horn XLR power cable (plugs into charger connection)(for Invacare & Quickie)	\$94.88
<b>LEG BAG EMPTIER</b>			
* LB2	___ A421	Electric leg bag emptier 2, complete switch control system	\$695.00
* LB2 21 ECU	___ A422	LB2 with UE1E ECU port option (for chairs with UE1E electronics)	\$695.00
* LB2 OTH ECU	___ A423	LB2 with ECU port option for other electronics	\$822.25
<b>LIGHTS</b>			
<u>Basic Lighting Package Models</u>			
* LP	___ A601	Safety illumination package (headlamp, universal taillights, switch & cables)	\$443.00
<u>Lighting Package Options (Up charges to basic lighting package)</u>			
* LP TIBB	___ A615	Supply LP with taillights in 21st grp 27 batt box cover	\$57.00
* LP 21H	___ A617	Supply LP for use with taillights on BOUNDER H-frame chairs	-\$75.00
* LP NO TL	___ A623	Supply red reflectors instead of universal taillight assembly	-\$70.00
* LP 2nd HL	___ A625	2nd headlamp and y cable for Lighting Package	\$150.00
LP PB SWITCH	___ A629	Supply LP with pushbutton switch instead of toggle switch, up charge	\$19.00
LP XLR PWR CBL	___ A630	LP XLR power cable (plugs into charger connection)(for Invacare & Quickie)	\$94.88
DUAL XLR PWR CBL	___ A630D	Dual XLR power cable (provides power for two accessories)(Invacare/Quickie)	\$158.12
<b>MIRROR</b>			
* MIRROR	___ A701	Detachable rear view mirror	\$96.00
<b>MOUNTS</b>			
MOUNT IPAD/IPAD2	___ A751	Universal wheelchair iPad/iPad2 mount, clamps around 0.625" to 1.50" dia tubing	\$96.00
MOUNT CELL	___ A753	Universal wheelchair cell phone mount, clamps around 0.625" to 1.50" dia tubing	\$96.00
MOUNT TAB 7	___ A754	7" Tablet mount, adjustable extension, clamps around 0.625" to 1.50" dia tubing	\$96.00
MOUNT TAB 10	___ A755	10" Tablet mount, adj extension, clamps around 0.625" to 1.50" dia tubing	\$160.00
MOUNT TAB 12	___ A756	12" Tablet mount, adj extension, clamps around 0.625" to 1.50" dia tubing	\$165.00
DRINK HLDER	___ A761	Drink Holder	\$60.00
<b>* POSITIONING STRAPS (Do not use as seat belts in vehicles)</b>			
PS FLIP LATCH	___ A801	Flip latch positioning strap (specify 45" or 60")	\$63.25
PS PUSH BUTTON	___ A802	Push button positioning strap (specify 45" or 60")	\$63.25
PS PINCH BUCKLE	___ A803	Pinch buckle positioning strap (specify 45" or 60")	\$63.25
PS VELCRO	___ A804	Velcro closure positioning strap (specify 45" or 60")	\$63.25
* PS CUSTOM	___ A805	Custom length positioning strap (up charge any strap other than 45" or 60")	\$56.93
<b>POWER CONVERTER</b>			
24/12PC	___ A831	24V to 12V power converter (5A maximum load)	\$575.00

IF \*, SEE NOTE LISTED BY STOCK NUMBER ON LAST PAGES

Part Number	Stock Qty Number	Part Description	Suggested Retail Price
SSAI	___ A841	Specialty switch accessory interface	\$632.50
<b>WHEEL LOCKS</b>			
WL	___ A851	Pair, super duty wheel locks for BOUNDER conventional frame chairs & gurneys (specify hi, center, or lo mount and if inverted)	\$151.80
WL HF	___ A852	Pair, super duty wheel locks for BOUNDER H-frame chairs	\$290.95
WLE	___ A853	Pair, wheel lock extensions	\$59.50

# ACCESSORIES

21st Century SCIENTIFIC, Inc. (800) 448-3680 (208) 667-8800 FAX (208) 667-6600

e-mail: 21st@wheelchairs.com www.wheelchairs.com

Slk# Note

## BATTERY CHARGERS

A135 BC12-6. 12.6V 6A AUTOMATIC BATTERY CHARGER. FOR USE WITH MANUAL CHAIRS WITH RECARO SEATS AND/OR 12V ACCESSORIES

## FAN

## HORN

A501 HORN. 24V SAFETY AUDIO ALERT, COMPLETE, FOR MOST 24V POWER WHEELCHAIRS. THIS 24V HORN IS LOUD! THE HORN BUTTON (CONTROL SWITCH) CAN BE MOUNTED ON THE WHEELCHAIR TUBING AT ANY CONVENIENT LOCATION. ONE SIZE FITS ALL WIDTH CHAIRS. COMPATIBLE WITH MOST 24V POWER WHEELCHAIRS. 1 YEAR WARRANTY INCLUDED. TOGGLE SWITCH TYPE HORN BUTTON WILL BE SUPPLIED UNLESS YOU SPECIFICALLY REQUEST A PUSHBUTTON SWITCH.

## LEG BAG EMPTIER

A421 LB2. ELECTRIC LEG BAG EMPTIER 2, COMPLETE SWITCH CONTROL SYSTEM. ALLOWS LEG BAG USERS TO DRAIN THEIR LEG BAGS WITHOUT ASSISTANCE. THIS OFTEN FACILITATES INCREASED FLUID INTAKE THAT CAN REDUCE THE LIKELIHOOD OF URINARY TRACT INFECTIONS. KIT INCLUDES EVERYTHING NEEDED FOR A COMPLETE INSTALLATION: 24V PINCH VALVE WITH MANUAL OVERRIDE, ANKLE STRAP (WITH VELCRO CLOSURE), DRAIN TUBE EXTENSION, CONTROL SWITCH, LEG CABLE, FUSED BATTERY CABLE, AND OWNER'S MANUAL. ALSO INCLUDES 10 BLACK PLASTIC CABLE TIES AND ADAPTERS FOR COUPLING THE DRAIN TUBE EXTENSION TO THE LEG BAG. CAN BE INSTALLED ON MOST 24V POWER WHEELCHAIRS. VALVE CAN BE WORN ON INSIDE OR OUTSIDE OF LEFT OR RIGHT ANKLE. TO MOUNT VALVE ON A FOOTPLATE, ALSO ORDER FOOTPLATE ADAPTER LISTED BELOW. SPECIFY IF TOGGLE SWITCH OR PUSHBUTTON SWITCH CONTROL IS DESIRED. 6 MONTH WARRANTY INCLUDED. LEG BAG NOT INCLUDED.

A422 LB2 21 ECU. LB2 WITH UE1E ECU PORT OPTION (FOR CHAIRS WITH UE1E ELECTRONICS). THIS OPTION REPLACES THE CONTROL SWITCH AND THE FUSED BATTERY CABLE WITH AN ECU PORT INTERFACE CABLE. REQUIRES A UE1E PROGRAMMER (NOT INCLUDED) TO PROGRAM THE ECU PORT.

A423 LB2 0TH ECU. LB2 WITH ECU PORT OPTION FOR OTHER ELECTRONICS. FOR INSTALLATIONS ON CHAIRS WITH THAT DO NOT USE 21ST UE1E ELECTRONICS. REDUCES CURRENT AND ELIMINATES VOLTAGE SPIKES TO PROTECT THE ECU PORT. THIS OPTION REPLACES THE CONTROL SWITCH WITH AN ECU PORT ADAPTER MODULE THAT PLUGS INTO THE ECU PORT. PROFESSIONAL INSTALLATION IS REQUIRED TO COMPLETE CONNECTION TO ECU PORT AND TO PROGRAM THE CHAIR'S ECU. CAN BE CONFIGURED FOR USE WITH DYNAMIC DX, INVACARE MARK IV AND OTHER ELECTRONICS.

## LIGHTS

### BASIC LIGHTING PACKAGE MODELS

A601 LP. SAFETY ILLUMINATION PACKAGE (HEADLAMP, UNIVERSAL TAILLIGHTS, SWITCH & CABLES). LP INCLUDES ONE 1900LM LED SEALED BEAM HEADLAMP, A TAILLIGHT ASSEMBLY, SWITCH, CABLES, MOUNTING HARDWARE AND OWNER'S MANUAL. CURRENT DRAW FOR HEADLAMP: .46A @ 24V; TAILLIGHT ASSEMBLY: 0.30A @ 24V; COMPLETE ONE HEADLAMP SYSTEM: .76A @ 24V. SECOND HEADLAMP CAN BE INSTALLED (ORDER A625 BELOW). 6 MONTH LIMITED WARRANTY INCLUDED (DOES NOT COVER BREAKAGE OR BURNOUT OF HEADLAMP, TAILLIGHT BULBS OR TAILLIGHT LENSES). TOGGLE SWITCH WILL BE SUPPLIED UNLESS PUSHBUTTON SWITCH IS SPECIFIED.

### LIGHTING PACKAGE OPTIONS (UP CHARGES TO BASIC LIGHTING PACKAGE)

A615 LP T1BB. SUPPLY LP WITH TAILLIGHTS IN 21ST GRP 27 BATT BOX COVER. FOR BOUNDER CONVENTIONAL (TUBULAR) POWER WHEELCHAIRS OR OTHER CHAIRS THAT HAVE A 21ST DUAL SLIDING GROUP 27 BATTERY BOX INSTALLED. INSTEAD OF SUPPLYING A UNIVERSAL TAILLIGHT ASSEMBLY, TAILLAMPS ARE BUILT INTO THE TOP OF THE BATTERY BOX COVER INSTEAD OF A SEPARATE TAILLIGHT CHASSIS. INCLUDES A NEW BATTERY BOX COVER. NOT FOR USE WITH BOUNDER H-FRAME CHAIRS.

A617 LP 21H. SUPPLY LP FOR USE WITH TAILLIGHTS ON BOUNDER H-FRAME CHAIRS. FOR USE ONLY WITH BOUNDER H-FRAME CHAIRS. PLUGS INTO TAILLIGHTS LOCATED IN THE H-FRAME TUBING.

A623 LP NO TL. SUPPLY RED REFLECTORS INSTEAD OF UNIVERSAL TAILLIGHT ASSEMBLY. NO TAILLAMPS ARE INCLUDED WITH THE SYSTEM. INCLUDES TWO RED REFLECTORS FOR MOUNTING ON THE REAR OF THE CHAIR.

A625 LP 2nd HL. 2ND HEADLAMP AND Y CABLE FOR LIGHTING PACKAGE. CURRENT DRAW FOR COMPLETE TWO HEADLAMP SYSTEM: 3.80A @ 24V. SUPPLIED WITH L-BRACKET, 7/8" OD TUBE CLAMP AND CABLE.

## MIRROR

A701 MIRROR. DETACHABLE REAR VIEW MIRROR. THIS DETACHABLE REAR VIEW MIRROR HAS A WIDE ANGLE CONVEX HEAD THAT ALLOWS USERS TO SEE TO THE REAR WITHOUT TURNING THEIR HEAD. IT INCREASES SAFETY IN TRAFFIC AND IS ALSO HANDY WHEN BACKING INTO OR OUT OF ELEVATORS. THE MIRROR COMES WITH MOUNTING BRACKET, ADJUSTABLE MAST AND A QUICK DETACH CLAMP. CAN BE MOUNTED ON MOST WHEELCHAIRS, MANUAL OR ELECTRIC.

## MOUNTS

### POSITIONING STRAPS (Do not use as seat belts in vehicles)

CAUTION! DO NOT USE AS SEAT BELTS OR RESTRAINTS IN LICENSED VEHICLES. POSITIONING STRAPS ARE TO BE USED ONLY FOR HOLDING USER IN POSITION WHILE DRIVING THE WHEELCHAIR. FOR WHEELCHAIRS, INDICATE WHETHER LAP OR CHEST MOUNT. FOR GURNEYS, INDICATE DISTANCE TO MOUNT STRAPS FROM FRONT OR REAR OF MATTRESS PAN, LENGTH OF STRAP, AND WHAT PART OF BODY STRAP IS TO GO AROUND.

Slk# Note

A805 PS CUSTOM. CUSTOM LENGTH POSITIONING STRAP (UP CHARGE ANY STRAP OTHER THEN 45" OR 60"). THIS ADDITIONAL CHARGE IS REQUIRED FOR ANY POSITIONING STRAP THAT IS NOT 60" LONG.

## POWER CONVERTER

## SPECIALTY SWITCH ACCESSORY INTERFACE

## WHEEL LOCKS